

SPECIFICATION SHEET

SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

SPECIFICATION SHEET NO.	S0312 - SBR303M825S022			
ORIGINAL MFG/PART NO.	TGS Crystals/SBR 303.825MA TLF/R303.825S22			
NEXTGEN PART CODE	SBR303M825S022 Indicate This Code For RFQ /Order			
DATE	Mar. 12, 2025			
REVISION	A2 Updated With Most Recent Data			
DESCRIPTION AND	SMD SAW Resonator, 6 Pads, 3838 Type, SBR Series			
MAIN PARBMETRICS	Case Code DCC6, Dimension L3.8*W3.8*H1.5mm Center Frequency 303.825MHz; Frequency Tolerance ±75KHz Insertion Loss: 1.1dB Typical, 1.8dB Max. Operating Temp. Range -40°C ~ +85°C Reflow Profile Condition 260°C Max. Package in Tape/Reel, 1000pcs/Reel REACH/RoHS/RoHS III Compliant			
CUSTOMER				
CUSTOMER PART NUMBER				
CROSS REF. PART NUMBER				
МЕМО				

VENDOR APPROVE

Issued/Checked/Approved







Effective Date: Mar. 12, 2025

CUSTOMER APPROVE	
------------------	--

Date:



SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

MAIN FEATURE

- SMD SAW Resonator 3838 Type 6 Pads
- Dimension L3.8*W3.8*H1.5mm
- Low-loss SAW Resonator
- One Port SAW Resonator
- Package Code DCC6
- Ceramic Package For Surface Mounted Technology (SMT)
- Electrostatic Sensitive Device (ESD)
- Moisture Sensitivity Level (MSL) 1
- Short Lead time
- · Cross Competitors Parts and More
- REACH/RoHS/RoHS III Compliant





Image shown is a representation only. Exact specifications should be obtained from the product dimension.





APPLICATION

- Bluetooth, Wireless Communication Set
- · Communication Electronics

ELECTRICAL CHARBCTERISTICS

- See Page 5
- All Products Parameters are Subject To NextGen Components' Final Confirmation.

SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

HOW TO ORDER

• Please Follow Up Part Code Guide And Indicate NextGen Part Code SBR303M825S022 For RFQ and Order.

PART CODE GUIDE




CODE	NAME	KEY SPECIFICATION OPTION
SBR	Series Code	SMD SAW Resonator, 6 Pads, 3838 Type Case Code DCC6, Dimension L3.8*W3.8*H1.5mm
303M825	Frequency Range Code	303M825: 303.825MHz
S022	Internal Control Code	Letter A~Z, a~z or Digits (1-9)
XX	Special/Custom Parameters Code	Blank: N/A XX: Letter A~Z, a~z or Digits (0~9) for Special/Custom Parameters



SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES


DIMENSION - Unit: mm, L3.8*W3.8*H1.5mm

Bottom View



PIN	CONFIGURATION
2	Input
5	Output
1, 3, 4, 6	Case Ground

Side View



SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

MAX. RATING & CHARACTERISTICS - At 25±2°C Ambient Temperature Unless Otherwise Specified.

PARAMETER	SYMBOLS	VALUE	UNITS
RF Power Level	Р	10	dBm
DC Voltage	VDC	±30	V
Operating Temperature Range	Та	-40 to +85	°C
Storage Temperature Range	Tstg	-55 to +125	°C

ELECTRONICAL CHARACTERISTICS


1) Test Temperature: $25^{\circ}C\pm2^{\circ}C$ 2) Terminating source impedance: 50Ω 3) Terminating load impedance: 50Ω .

PARAMETER		SYMBOLS	CHARACTERISTICS			
			MIN.	TYPICAL	MAX.	UNIT
Center Frequency- Absolute Frequency		FC	-	303.825	-	MHz
Frequency Tolerance from 303.825MHz		∆fc	-	±75	-	KHz
Insertion Loss	Insertion Loss		-	1.1	1.8	dB
Quality	Unloaded Q	Qυ	-	16411	-	
Factor	50Ω Loaded Q	QL	-	1986	-	
Frequency Aging	Absolute Value during the 1 st Year	fA	-	≤10	-	ppm/yr
DC Insulation Resistance between Any Two Pins			1.0	-	-	ΜΩ
	Motional Resistance	RM	-	13.3	18	Ω
RF Facility along	Motional Inductance	LM	-	122.3	-	μН
Equivalent RLC Model	Motional Capacitance	СМ	-	2.24	-	fF
	Static Capacitance	C0	2.6	2.8	3.0	pF




SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

MEASUREMENT CIRCUIT – FOR REFERENCE ONLY




RECOMMENDED SOLDERING PROFILE – FOE REFERENCE ONLY






TYPICAL LOW-POWER TRANSMITTER APPLICATION - FOE REFERENCE ONLY



TYPICAL LOCAL OSCILLATOR APPLICATION - FOE REFERENCE ONLY






FREQUENCY RESPONSE - FOR REFERENCE ONLY



EQUIVALENT LC MODEL – FOR REFERENCE ONLY



3/12/2025


SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

RELIABILITY CHARACTERISTICS

TEST ITEMS	TEST METHOD AND CONDITIONS
Temperature Storage	• Temperature: $85^{\circ}C\pm2^{\circ}C$, Duration: $250h$, Recovery time: $2h\pm0.5h$ • Temperature: $-40^{\circ}C\pm3^{\circ}C$, Duration: $250h$, Recovery time: $2h\pm0.5h$
Humidity Test	• Conditions: 60°C±2°C, 90~95% RH, Duration: 250h
Thermal Shock	 Heat cycle conditions: TA=-40°C±3°C, TB=85°C±2°C, t1=t2=30min, Switch time: ≤3min, Cycle time: 100 times, Recovery time: 2h±0.5h.
Vibration Fatigue	 Frequency of vibration: 10~55Hz, Amplitude:1.5mm Directions: X,Y and Z, Duration: 2h
Drop Test	Cycle time: 10 times, Height: 1.0m
Solderability	• Temperature: 245°C±5°C, Duration: 3.0s5.0s, Depth: DIP2/3 , SMD1/5
Resistance to Soldering Heat	 Thickness of PCB:1mm , Solder condition: 260°C±5°C , Duration: 10±1s Temperature of Soldering Iron: 350°C±10°C , Duration: 3~4s , Recovery time : 2 ± 0.5h
Remarks	 As a result of the particularity of inner structure of SAW products, it easy to be breakdown by electrostatic, so we should pay attention to ESD protect in the test. Static voltage between signal load and ground may cause deterioration and destruction of the component. Please avoid static voltage. Ultrasonic cleaning may cause deterioration and destruction of the component. Please avoid ultrasonic cleaning. Only leads of component may be soldered. Please avoid soldering another part of component. There is a close relationship between the device's performance and matching network. The specifications of this device are based on the test circuit shown above. L and C values may change depending on board layout. Values shown are intended as a guide only.


SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

TAPE DIMENSION - Unit: mm, All Devices are packed in accordance with EIA standard RS-481-2.



* B0: 5.35 for QCC8C; 4.15 for DCC6/QCC8B; 3.35 for DCC6C/QCC8D

REEL DIMENSION - Unit: mm, 1000pcs/Reel.



SMD SAW RESONATOR 6 PADS 3838 TYPE SBR SERIES

IMPORTANT NOTES AND DISCLAIMER

- ROHS COMPLIANCE: The levels of RoHS restricted materials in this product are below the maximum
 concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an
 exempted application, in accordance with EU RoHS Directive (EU) 2015/863 EC (RoHS3). RoHS Test Report for
 this product can be obtained can be obtained at Download Center.
- REACH COMPLIANCE: REACH substances of high concern (SVHCs) information is available for this product.
 Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, REACH Test Report for this product can be obtained at Download Center.
- All Product parametric performance is indicated in the Electrical Characteristics for the listed herein test
 conditions, unless otherwise noted. Product performance may not be indicated by the Electrical
 Characteristics if operated under different conditions.
- 4. NextGen Component, Inc (*NextGen*) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- 5. NextGen makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does NextGen assume any liability for application assistance or customer product design.
- 6. NextGen does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application. No license is granted by implication or otherwise under any intellectual property rights of NextGen.
- 7. NextGen products are not authorized for use as critical components in life support devices or systems without express written approval by NextGen.
- 8. NextGen requires that customers first obtain an RMA (Returned Merchandise Authorization) number prior to returning any products. Returns must be made within 30 days of the date of invoice, be in the original packaging, unused and like-new condition. At the time of quoting or purchasing, a product may say that it is Non-Cancelable/ Non-Returnable (NCNR). These products are not returnable and not refundable.